

The Nimble Thermal Conductivity Meter



Key Features

- Thermal conductivity range: 0.03 to 40 W/m/K.
- Sample size: minimum 10 mm thickness and 30 mm diameter.
- High accuracy and measurement stability.
- Hot Disk sensor and sample holder included.
- Hot Disk advanced software for in-depth data analysis, including thermal diffusivity and specific heat capacity.
- Quick-Start Guide: begin testing within minutes.
- Ideal teaching tool at school & university laboratories.
- Light and nimble - easily carried.
- Wireless control through WiFi connection to PC is available optionally.

Contact information

Hot Disk International Sales:
www.hotdiskinstruments.com
info@hotdisk.se
Phone + 46 31 411 410

Hot Disk AB
Sven Hultins gata 9A
SE-412 88
Gothenburg
Sweden